

94. Recommended spare parts: CM, CME

50/60 Hz

Customer information

Project title:	Customer name:
Reference number:	Customer number:
Customer contact:	Customer phone number: ()
	Fax number: ()

Pump information

Type	1	P _{max}	6	bar	6	PSI	6	MPa		
Model	2	T _{liq,max}	7	°C	7	°F				
Env	3	IP	4	T _{Amb}	5	°C	5	°F		
				Insulation class	8		9			
50 Hz	Q _{nom}	10	m ³ /h	10	GPM	Q _{nom}	10	m ³ /h	10	GPM
	H _{nom}	11	m	11	PSI	H _{nom}	11	m	11	PSI
	H _{max}	12	m	12	PSI	H _{max}	12	m	12	PSI

Quotation made by

Company name:

Prepared by:

Phone number: ()

Fax number: ()

Date:

Quote number:

Motor information

50 Hz	1	~	2	/	2	V	60 Hz	1	~	2	/	2	V
I _{max}	3	/	3	A	I _{max}	3	/	3	A				
I _{1/2}	4	/	4	A	I _{1/2}	4	/	4	A				
P ₂	5	kW	5	HP	P ₂	5	kW	5	HP				
Capacitor	6	uF / V	Capacitor	6	uF / V								

CE GRUNDFOS X

Pump and motor

Spare part/service kit	Recommended spare parts/service kits for...		
	2 years operation	5 years operation	Product number of part/kit
Gasket and seal kit	1 kit	2 kits	
Repair kit, neck ring	1 kit	2 kits	
Motor bearing kit	-	1 kits	