



# WELL-X-TROL® WX-400 Series (Non-ASME)

150 PSIG Working Pressure

## Non-ASME Models


Model No.	Tank Vol.		Max. Accept. Factor	A Height		B Diameter		C Inset		D Conn.Centerline		E ins.	Sys. Conn. ins.	Ship Wt.	
	Lit.	Gal		mm	ins.	mm	ins.	mm	ins.	mm	ins.			kg	lbs.
WX-401	68	18	.65	794	31¼	413	16¼	124	4 <sup>7</sup> / <sub>8</sub>	38	1½	12¾	1	43	95
WX-402	95	25	.45	1010	39¾	413	16¼	124	4 <sup>7</sup> / <sub>8</sub>	38	1½	12¾	1	51	112
WX-403	129	34	.33	1251	49¼	413	16¼	124	4 <sup>7</sup> / <sub>8</sub>	38	1½	12¾	1	56	123
WX-404	258	68	.50	1200	47½	610	24	159	6¼	41	1 <sup>5</sup> / <sub>8</sub>	16	1¼	95	210
WX-405	341	90	.39	1505	59¼	610	24	159	6¼	41	1 <sup>5</sup> / <sub>8</sub>	16	1¼	127	280
WX-406	417	110	.31	1778	70	610	24	159	6¼	41	1 <sup>5</sup> / <sub>8</sub>	16	1¼	152	335
WX-407	500	132	.35	1435	56½	762	30	254	10	41	1 <sup>5</sup> / <sub>8</sub>	24	1¼	207	456

## Maximum Operating Conditions

Operating Temperature	200° F (93° C)
Working Pressure	150 PSIG (10.5 bar)

## Specifications

Description	Standard Construction
Shell	Steel
Diaphragm	Heavy Duty Butyl/EPDM ANSI/NSF61
System Connection	Malleable Iron (NPT)
Liner	Polypropylene
Coating	Red Oxide Primer
Factory Precharge	30 PSIG (2.2 bar)



All dimensions and weights are approximate.

Job Name \_\_\_\_\_  
 Location \_\_\_\_\_  
 \_\_\_\_\_  
 \_\_\_\_\_  
 Engineer \_\_\_\_\_  
 Contractor \_\_\_\_\_  
 Contractor P.O. No. \_\_\_\_\_  
 Sales Representative \_\_\_\_\_

Model No. Ordered \_\_\_\_\_  
 System Pressure Range \_\_\_\_\_  
 Pre-Charge Pressure \_\_\_\_\_  
 Pump GPM \_\_\_\_\_  
 Date Submitted \_\_\_\_\_