

Grundfos submersible pumps – more than stainless steel



- Complete range with flow rates of 0-475 m³/h
- State-of-the art hydraulics provide high efficiency and low operating costs
- 100% stainless steel inside and outside
- Sand resistant
- Resistant to aggressive water
- Motor burnout protection
- Dry-running protection
- Monitoring and communication via CU 3 remote control